

8 Port Rackmount KVM Console w/ 6ft Cables - Integrated KVM Switch w/ 17" LCD Monitor - Fully Featured 1U LCD KVM Drawer- OSD KVM - Durable 50,000 MTBF - USB + VGA Support

Product ID: RKCONS1708K



Providing centralized control of up to eight servers, this 8-port rackmount KVM console gives you easy access to your systems. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rack space.

The 1U rackmount console features a built-in keyboard, a touchpad for intuitive control, and a 17-inch LCD display that supports resolutions up to 1280x1024.

This 8-port KVM console comes with everything you need to set up right out of the box:

- 8 VGA KVM Cables
- Mounting Rails
- M5 Cage Nuts and Screws

With direct access to eight systems or servers, the 8-port KVM module gives you the flexibility you need to easily integrate the console into your existing server infrastructure.

Rack consoles provide convenient, rack-mounted control options for single servers or the entire server room. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. The RKCONS1708K is backed by a StarTech.com 2-year warranty and free lifetime technical support

Certifications, Reports and Compatibility















Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

Features

- TECH SPECIFICATIONS: Rackmount KVM Console, 17" Active Matrix TFT LCD Monitor, 1280 x 1024, 8 port VGA KVM switch w/ 6 ft. cables, 99 key full keyboard + numeric keypad & trackpad; Supports USB 2.0
- PROFESSIONAL & SECURE: Customizable hot-keys, on-screen display (OSD), multi-level user security, user access levels / port permissions, & auto scan
- INTEGRATED DESIGN: Combines a KVM + Console w/ integrated power supply into 1U of rack space allowing space for other equipment. Mount depth: 22" [56 cm] to 35" [90 cm] (incl. mounting hardware)
- HEAVY DUTY: LCD KVM drawer has durable steel construction and heavy duty rail design that supports frequent use in operating environments from 0C to 40C (32F to 104F) with an MTBF of 50,000 hours
- TESTED & PROVEN: This OS independent rack console is universally compatible w/ leading servers and backed by a StarTech.com 2-year warranty and free lifetime 24/5 multilingual technical support

Hardware		
	Warranty	2 Years
	U Height	1U
	Front Door Key Lock	No
	Audio	No
	Display Size	17in
	Panel Type	Active Matrix TFT LCD
	KVM Ports	8
	PC Interface	USB
	PC Video Type	VGA
	Number of Monitors Supported	1
	Rack-Mountable	Yes



Cables Included Yes

Daisy-Chain No

Performance

On-Screen Display Yes

IP Control No

Maximum Analog

Resolutions

1280 x 1024

Supported Resolutions Resolutions up to 1280 x 1024 @ 60Hz

Aspect Ratio 5:4

Response Time 5ms

Contrast Ratio 1000:1

Brightness 250 cd/m

Color Depth 8-bit, 16.7M colors

Pixel Pitch Support 0.264 x 0.264 mm

Viewing Angle 170 (H), 160 (V)

Maximum Number of

Users

1

Port Selection Support Push Button, Hotkeys, and OSD (On Screen Display)

MTBF 50, 000 Hrs

Connector(s)

Console Interface(s) 1 - VGA (15 pin, High Density D-Sub)

2 - USB 2.0 Type-A (4 pin, 480Mbps)

Host Connectors 8 - VGA (15 pin, High Density D-Sub)

Other Interface(s) 1 - 15 Pin High Density D-Sub

Special Notes / Requirements

Note The minimum mounting depth of this rackmount console is less

than the length of the console itself. Please consider the length of the rackmount console when evaluating if it will fit into your

rack.



Indicators

LED Indicators 8 - Green/Red - Online/Selected LED

Power

Power Source International Power Cords

Input Voltage 100 - 240 AC

Input Current 1.5A

Power Consumption (In

Watts)

17W

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 10 ~ 80% RH

Physical Characteristics

Color Black

Material Steel

Cable Length 6 ft

Product Length 24.5 in [62.3 cm]

Product Width 1.9 in [4.8 cm]

Product Height 1.7 in [4.2 cm]

Weight of Product 37.6 lb [17.0 kg]

Maximum Mounting Depth 35.4 in [90 cm]

Minimum Mounting Depth 22.0 in [56 cm]

Packaging Information

Package Quantity 1

Package Length 24.3 in [61.7 cm]

Package Width 3.0 in [7.6 cm]



	Package Height	7.2 in [18.2 cm]
	Shipping (Package) Weight	43.5 lb [19.7 kg]
What's in the Box		
	Included in Package	1 - KVM console
		8 - KVM cables
		8 - M5 cage nuts
		8 - M5 screws
		5 - Power Cords (NA, JP, UK, EU, ANZ)
		2 - Mounting Rails
		1 - Quick-Start Guide

^{*}Product appearance and specifications are subject to change without notice.