

Scotch® Fine Line Tape 218



Technical Data

December, 2007

Product Description

Scotch® Fine Line Tape 218 is a high-performance film backed tape with low profile and high adhesion to achieve excellent paint lines and for other masking and holding applications.

Product Construction

Backing	Adhesive	Color	Standard Roll Length
Polypropylene plastic film	Rubber adhesive with an ideal balance of properties for masking use	Green, matte finish	60 yds. (54.9 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	37 oz./in. width (40 N/100 mm)	D-3330
Tensile Strength:	13 lbs./in. width (228 N/100 mm)	D-3759
Elongation at Break:	720%	D-3759
Tape Thickness:	5.0 mils (0.13 mm)	D-3652
Temperature Use Range:	Up to 250°F (121°C) for 30 minutes	

Features

- Will give an excellent color line separation due to its thinness.
- The specially processed film backing stretches easily for smooth curves, yet can be easily torn by hand with a quick tearing action.
- Specially processed film backing will allow taping over fresh paint jobs sooner than paper tapes with less chance of imprint damage.
- Has excellent moisture and solvent resistance.
- Not considered a high temperature tape but could be used on bake cycles up to 250°F (121°C) for up to 30 minutes.
- Should not be subjected to outdoor exposure or prolonged periods of sunlight as tape may become difficult to remove.

Scotch® Fine Line Tape

218

Application Ideas

- Fine Line paint masking
- Circuit board conformal coat masking
- Electroplating stop off masking, non-critical
- Circuit board splash mask protection
- Moisture resistant masking
- Can sealing
- Solvent resistant masking
- Silk screen masking
- Lettering
- Labeling (surface writable)

Storage

Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within one year from date of manufacture.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.

3M

Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Scotch is a registered trademark of 3M.
Printed in U.S.A.
©3M 2007 70-0709-4628-3 (12/07)