

405.MT | MICRO-TECH® "COMPACT" CUTTERS: HANDLING




Norm :

NF ISO 9654, ISO 9654, DIN ISO 9654, ASME B107.500


Description :

- These pliers combine cutting performance with accessibility thanks to their new slim diagonal shape.
- Fall prevention models avoid wire ejection. The 405.MT pliers allow to cut piano wire up to 0.4 mm.



Informations :

	405.MT
B [mm]	10,5
C [mm]	9,5
E [mm]	7
L [mm]	110
Cut	h
Cu - Ni Ø [mm]	0,3 - 1,3
Bits	212.E25
Fe 30 HRc diam. [mm]	0,7

	405.MT
Piano Diameter [mm]	0,4
Offcut retainer	-
[g]	60