

Pin Header DIN 41651, 90°



FEATURES:

- Fully shrouded header assembly
- 2.54 mm x 2.54 mm long lock
- Right angle type
- Gold flash plating

SPECIFICATION:

Contact material	Copper alloy, gold-plated
Connection principle	Wire-board
Gender of contacts	Male
Temperature range	-40 ... +105 °C
Pitch	2.54 mm
Insulation material	Polyester, UL 94V-0
Contact resistance	20 mΩ max.
Insulation resistance	1000 MΩ min.
Dielectric voltage	500 VAC
Contacts	10
Dim.A	31.9 mm
Dim.B	10.1 mm
Dim.C	18 mm
Rated current	3 A

