

# Mini USB Connector, SMT

5P



Mini USB female connector  
SMT type  
Insulator colour: black  
Shell finish: nickelage

## SPECIFICATION:

Poles	5
Insulator	Liquid-Crystal Polymer (LCP), UL 94 V-0
Shell	Brass
Temperature range	-55 ... +85 °C
Rated current	1 A
Contact material	Copper Alloy, Gold-Flashed
Dielectric withstand voltage	100 VAC
Insulation resistance	100 MΩ min.
Contact resistance	50 mΩ max.

## Art. Nr.

**RND 205-00861**

