

Pin Header DIN 41651, 90°

FEATURES:

Fully shrouded header assembly
 2.54 mm x 2.54 mm short lock
 Right angle type
 Gold plating
 Low-lead

SPECIFICATION:

Contact material	Copper alloy, gold-plated
Connection principle	Wire-board
Gender of contacts	Male
Temperature range	-40 ... +105 °C
Pitch	2.54 mm
Insulation material	Polyester, UL 94V-0
Contact resistance	20 mΩ max.
Insulation resistance	1000 MΩ min.
Dielectric voltage	500 VAC
Contacts	20
Dim.A	44.7 mm
Dim.B	34.5 mm
Dim.C	22.8 mm
Rated current	3 A

