

Jumper

SPECIFICATION:

Contact material	Gold-Plated Brass
Connector design	Jumper
Gender of contacts	Female
Temperature range	-55 ... +105 °C
Pitch	2.54 mm
Contact resistance	30 mΩ
Insulation resistance	1000 MΩ min. at DC 500 V
Dielectric withstand voltage	600 VAC at sea level
Contacts	2
Dim.A	13.5 mm
Dim.B	2.4 mm
Dim.C	5 mm
Rated current	3 A

