

Jumper

SPECIFICATION:

Contact material	Gold-Plated Brass
Connector design	Jumper
Gender of contacts	Female
Temperature range	-55 ... +105 °C
Pitch	2.54 mm
Insulator	PBT + 30% glass fiber
Contact resistance	20 mΩ min. at DC 100 mA
Insulation resistance	100000 MΩ min. at DC 500 V
Dielectric voltage	750 VAC for 1 min.
Contacts	2
Dim.A	6.5 mm
Dim.B	2.4 mm
Dim.C	5 mm
Rated current	3 A

