

USB Type A Connector

4P



USB A/F double connector
R/A type
Insulator colour: black
Shell finish: nickelage

SPECIFICATION:

Poles	4
Housing material	Steel, UL 94 V-0
Temperature range	-55 ... +85 °C
Rated current	1.5 A
Contact material	Copper alloy, Gold-plated
Dielectric withstand voltage	500 VAC
Insulation resistance	1000 MΩ min.
Contact resistance	30 mΩ max.

Art. Nr.

RND 205-00859

