

Pin Header DIN 41651



FEATURES:

- Fully shrouded header assembly
- 2.54 mm x 2.54 mm long lock
- Straight type
- Gold flash plating

SPECIFICATION:

Contact material	Copper alloy, gold-plated
Connection principle	Wire-board
Gender of contacts	Male
Temperature range	-55 ... +105 °C
Pitch	2.54 mm
Housing material	PBT, UL 94V-0
Rated current	3 A
Insulation resistance	1000 MΩ min. at 1000 VDC
Dielectric voltage	1000 VAC RMS for 1 min.

Article Nr.	Contacts	Dim.A	Dim.B	Dim.C
RND 205-00801	10	32 mm	27.9 mm	10.1 mm
RND 205-00804	14	37 mm	33 mm	15.2 mm
RND 205-00807	20	44.7 mm	40.6 mm	22.8 mm
RND 205-00809	26	52.3 mm	48.2 mm	30.4 mm
RND 205-00812	34	62.4 mm	58.4 mm	40.6 mm
RND 205-00815	40	70.1 mm	66 mm	48.2 mm

