

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013841](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Cover, Die-cast Aluminum, with 4 Pegs, without Gasket, Size 24B «104x27», Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Comments With nylon wire tether line.
 Component Size 24B «104X27»
 Component Type Cover
 IP Rating IP66
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type STD
 UPC 887191865317

Physical

Cover Coating Polyester Powder
 Cover Color Grey RAL 7037
 Lock to Mating Part Yes
 Material - Cover Die-cast Aluminum
 Material - Peg Stainless Steel
 Net Weight 65.400/g
 Number of Pegs 4
 Packaging Type Bag
 Thread Size N/A
 Thread Type N/A

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7824.6807.0



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size 24B «104x27» Housings with 2 Levers

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3841](#)