

Combination pH Electrode and TDS/EC Probe for HI 991300 & HI 991301

Code		HI 1288
Body		Polypro
Reference	Junction	single
	Cell	gel
Junction	Type	fiber
Tip	Shape	sphere
	Dimension	Ø5.0 mm
Plug	Type	DIN
Cable		7 wire
Temp range °C		0/+60
Pressure PSI/BAR		7.25/0.5
