



EMPTY ENCLOSURE

# TG ABS 2516-12-o

## TG ABS 2516-12-o

Empty enclosure

**CUSTOMIZE**

252 x 162 x 120 mm  
Article number: 10091201

Empty enclosure, Base and cover: ABS, light grey similar to RAL 7035, with quick closing, with cover retainer



## Technical data

### Measures

Width:	252 mm
Length:	162 mm
Height:	120 mm
Inner height:	104 mm

### Material:

Box:	ABS, grey similar RAL 7035
Cover:	ABS, grey similar RAL 7035
Sealing:	Polyurethane
Cover screw:	stainless steel V2A, fast-closing
material:	ABS

## Accessory

- DAE M12 - Pressure balance element
- LFR - Stepped drill
- NS 35-220 - Standard rail
- TG ABL - External fixing lugs kit
- TG DVS-57 - Cover retainer
- TG ISS - Interior hinge set
- TG MPI-2516 - Mounting plate
- TG MPS-2516 - Mounting plate
- TG PST2 - Sealing kit
- TS 15-220 - Standard rail



EMPTY ENCLOSURE

# TG ABS 2516-12-o

## Other attributes

Ingress protection:	IP66/IP67 acc. EN 60529 / DIN VDE 0470-1
Protection class:	II - isolate protection acc. VDE 0106
Impact resistance:	IK07 acc. DIN EN 5012 / VDE 0470 Part 100
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Cable entries:	No
Combustion behaviour acc. to UL 94:	HB acc. UL94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
weatherproof:	No

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%