



HM-30

Order No.: 23.2680

Price upon request

PRODUCTINFOS

Dynamic headband microphone

- For vocal and speech applications which require free movement
- Microphone windshield

TECHNICAL SPECIFICATIONS

HM-30

Type	headband microphone
Transmission method	cable
Polar pattern	cardioid
System	dynamic
Audio frequency range	300-16,000 Hz
Nominal impedance	500 Ω
Sensitivity	1 mV/Pa

HM-30

Admiss. ambient temp.	0-40 °C
Weight	80 g
Cable	3.5 m
Connection	3.5 mm plug, adapter 6.3 mm