

Han A Hood Top Entry HC 2 Levers PG 21



Part number	09 20 032 0430
Specification	Han A Hood Top Entry HC 2 Levers PG 21
HARTING eCatalogue	https://b2b.harting.com/09200320430

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hood
Type	High construction

Version

Locking type	Double locking lever (on the hood)
Han-Easy Lock®	Yes
Size	32 A
Version	Top entry
Cable entry	1x Pg 21
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate



Pushing Performance

Material properties

	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	297.2 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors