

Mini Push Button Switch

Q-937


TYPE: **PB-22E16**




SPECIFICATIONS

Contact Type	2PST
Rating	DC 30V, 30mA
Contacts Resistance	50mΩ Max
Insulation Resistance	100MΩ Min
Minimum Load	DC 250V
Dielectric Strengths	AC 250V / 1 minute
Life Test	100 000 Cycles Min
Operating temperature range	-25°C to +70°C
Operation Force	160 ± 50gf


Outline Drawing



Mounting



Circuitry



ON – OFF

