

Adapter - HC-NPT-1/2-M20 - 1686847


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M20 to 1/2"

RoHS

Key Commercial Data

Packing unit	25 pc
GTIN	 4 017918 822705
GTIN	4017918822705
Weight per Piece (excluding packing)	0.032 kg
Custom tariff number	74199990
Country of origin	Germany

Technical data

Dimensions

Length	25 mm
Length without connecting thread	18.5 mm
Connecting thread diameter	20 mm
Length of the connecting thread	6.5 mm

Ambient conditions

Degree of protection (IP)	IP68 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Brass, nickel-plated
Cable gland material	Nickel-plated brass
O-ring material	NBR
Thread type connection side	M20
Thread type on seal side	1/2-inch NPT
Thread type on connection side	M20

Adapter - HC-NPT-1/2-M20 - 1686847

Technical data

General

Color	silver
-------	--------

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27439207
eCl@ss 8.0	27439207
eCl@ss 9.0	27430314

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938
ETIM 6.0	EC000938
ETIM 7.0	EC000938

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Adapter - HC-NPT-1/2-M20 - 1686847

Approvals

Ex Approvals

Approval details

EAC



RU C-
DE.AI30.B.01102