




# Connectivity Solutions


## Product Detail



<b>Product Line:</b>	<a href="#">Aim</a> (Click for customer service)
<b>Part Number:</b>	24-328P
<b>Description:</b>	PRO COAX RATCHET CRIMPER,SMA/SMB,RG58/178
<b>Product Family:</b>	TOOLS&TESTERS_CRIMP TOOLS&DIES_COAXIAL RATCHET TOOL-PRO SERIES
<b>For Cables:</b>	RG58,RG142,RG174,RG188,RG223,RG303,RG316,RG400
<b>For Connector Type:</b>	BNC / TNC / FIBER
<b>Standard Pack:</b>	1

20070523-1523

## Standard Series Ratchet Crimping Tools by **Prestige**



*This series of tools offers a wide selection of interchangeable dies, a high quality steel frame with a full cycle ratchet mechanism and a quick release safety latch. All are blister packaged for retail display.*

Tool Part No.	Cable Size	Description	Size	Die Part #
24-328P	RG-58, RG-161, RG-178, RG-182, RG-188, RG-316	SMA, SMB, Fiber	.043", .069", .100" .128", .151", .210"	99-328
24-8856P	RG-6, RG-8 RG-59, RG-62	Crimps BNC-TNC 3 pc. Connectors with standard rings	.390", .275", .065"	99-8856
24-8857P	RG-58, RG-58AU RG-174, RG-139, RG-185 RG-188, RG-316	Crimps BNC-TNC 3 pc. Connectors with standard rings	.235", .128", .065"	99-8857
24-8858P	RG-58, RG-58AU, RG-59	Crimps BNC-TNC Teflon, RG-62 Teflon & 3 pc. Connectors also crimps 1/2" ring 'F' Connectors	.325", .210", .065"	99-8858
24-8859P	RG-59, RG-62 Belden 8281	Crimps BNC-TNC 2 & 3 pc. Connectors with standard & dual crimp rings	.325", .258", .065"	99-8859
24-8789P	RG-58, RG-59, RG-62, RG-58TFE, RG-59TFE, RG-62TFE	Crimps BNC & TNC 2 & 3 pc. Connectors with standard crimp rings by AMP, Kings and Amphenol	.257", .210", .060"	99-8789
24-9858P	RG-58, RG-59TFE	Crimps 2 pc. BNC & TNC Connectors	.320", .211"	99-9858
24-9859P	RG-59, RG-62	Crimps 2 pc. BNC & TNC Connectors	.320", .250"	99-9859
24-9958P	RG-58, RG-58TFE, RG-59TFE, RG-141TFE, RG-142, RG-223, RG-400 RG-303, RG-55	Crimps 3 pc. BNC-TNC & Mini-UHF Connectors	.213", .060"	99-9958
24-9959P	RG-59, RG-62, RG-450	Crimps 3 pc. BNC-TNC Proflex, RG-8X & Mini-UHF Connector	.255", .060"	99-9959
24-9912P	RG-122, 180, 34M RG-195, 8218, RG-174 188, RG-179, 187, 316	Crimps 3 pc. BNC-TNC Connectors	.184", .060"	99-9912
24-8644P	Open Barrel Crimper V.35 Contacts, 10-22 AWG	Crimps open barrel Non-insulated Connectors D-sub, Mini pins & sockets	-----	99-8644
*99-frame-9"	-----	9" Frame for Standard Ratchet Tools	-----	

\*Note: All standard series dies on this page are interchangeable with this Tool Frame.

## You-Design-It Ratchet Crimp Kit

*Designed by you for use with most Emerson or other brand RF connectors including 2 & 3 piece BNC, TNC and MiniUHF Connectors. Just choose any additional 3 dies from the standard series list to complete the kit.*

### Kit includes:

- (1) 24-9958P Ratchet Crimp Tool
- (1) 24-7734P Universal Coax Stripper
- (1) 24-7378P Heavy Duty Cable Cutter
- (1) 24-8810 Durable Plastic Case
- (3) 99-xxxx Select any three dies from this page to complete kit.



## Offset Ratchet Crimping Tools



**Ratchet Crimping Tool**  
for 2- & 3-Piece Crimp Connectors.  
*Offset die with 3 crimp sizes for Pins & Connector Ferrule including 'F' Connectors and RG-58 & 59TFE Cable. Features adjustable crimp pressure and quick release safety latch.*

Part No.	Replacement Die
24-8861P	99-8861

Hex Size	Use For
.060"	Center Conductor
.210"	Ferrule for RG-58/141/303/55/142/233/400
.320"	Ferrule for RG-6/143/212/222/Belden 8281,9231,9141



**Ratchet Crimping Tool**  
for 3-Piece Crimp Connectors.  
*Offset die with 3 crimp sizes for Pins & Connector Ferrule including RG-58 & 59TFE Cable. Features adjustable crimp pressure and quick release safety latch.*

Part No.	Replacement Die
24-8860P	99-8860

Hex Size	Use For
.060"	Center Conductor
.210"	Ferrule for RG-58/141/303/55/142/233/400
.255"	Ferrule for RG-59/62/140/210/Belden 8279