

## Datasheet

### Type G - British 2 Gang Distribution Unit 2m Cable Filtered, 10A, 230 V ac With Rcd Protection Fused

RS Stock 374-171



#### Specification:

Voltage Rating (Nominal)	230V rms
Maximum Current Rating	13A (7A Fuse fitted)
Power Consumption	Negligible
Lead Length	2m
Surge Handling (8/20us) [Per Element]	13.5kA [4.5kA]
Average Attenuation, Symmetric 1-30MHz (dB)	-20
Voltage Protection Level (U <sub>p</sub> ) 8/20us	900V@3kA 8/20us
Response Time	<10ns
BS6651:1999 Annex C Location Category	A & B