



Click [here](#) for the 3D model.

Dimensions	
D	17mm MAX
T	9.1mm MAX
LL	9mm +/-3mm
S	7mm NOM
Wire Size	0.6mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	700
Component Weight	4 g

General Information	
Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	20 (K) Temperature Rise Max.
Core	Fe-Si

Specifications	
Inductance	43 uH
Inductance Tolerance	20%
Current	2 A
Temperature Range	-40/+125°C
DC Resistance	54.1 mOhms