



Click [here](#) for the 3D model.

Dimensions	
D	26mm MAX
T	12.4mm MAX
LL	9mm +/-3mm
S	9mm NOM
Wire Size	1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	240
Component Weight	14 g

General Information	
Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	25 (K) Temperature Rise Max.
Core	Fe-Si

Specifications	
Inductance	51 uH
Inductance Tolerance	20%
Current	5 A
Temperature Range	-40/+125°C
DC Resistance	28 mOhms