


ROLINE Patchcord Cat.5e FTP



Description	<p>Patch cable for networking connections between RJ devices. Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends</p> <p>Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts</p> <p>Contact settings 1:1, in accordance with the EIA/TIA 568 standard</p> <p>Construction: 4-pair stranded copper wire.</p> <p>Complete shielding with aluminium clad polyester foil</p> <p>Standard: Cat5e / Class D</p> <p>Cover material PVC no LSOH</p> <p>Length indication on the sleeve</p> <p>2-year guarantee stand for performance promise</p>
Shield type	Foiled Twisted Pair
Impedance	100 Ohm
Transfer quality	Cat5e /Class D
Cross selection	4P AWG26 CMX (UL) CMH E164469-F3
Standards	ISO/IEC 11801 & EN

Article No RJ45 patch cord Cat.5e shielded, wiring 1:1

Length	grey	red	yellow	green	blue	black
0.5 m	21.15.0100	21.15.0181	21.15.0182	21.15.0183	21.15.0184	21.15.0185
1.0 m	21.15.0101	21.15.0131	21.15.0132	21.15.0133	21.15.0134	21.15.0135
2.0 m	21.15.0102	21.15.0141	21.15.0142	21.15.0143	21.15.0144	21.15.0145
3.0 m	21.15.0103	21.15.0151	21.15.0152	21.15.0153	21.15.0454	21.15.0155
5.0 m	21.15.0105	21.15.0161	21.15.0162	21.15.0163	21.15.0164	21.15.0165
7.0 m	21.15.0107	n/a	n/a	n/a	n/a	n/a
10 m	21.15.0110	21.15.0451	21.15.0452	21.15.0453	21.15.0454	21.15.0455
15 m	21.15.0115	21.15.0461	21.15.0462	21.15.0463	21.15.0464	21.15.0465
20 m	21.15.0120	21.15.0471	21.15.0472	21.15.0473	21.15.0474	21.15.0475

