


BU-1404940

(12 Position Male to Female Receptacle Shielded Cable Assembly, 16.4')



J1 Male



J1 Female



J1	Twist Pair	COLOR	J2
1	Twist Pair 1	WHITE	1
3		BROWN	3
6	Twist Pair 2	GREEN	6
4		YELLOW	4
5	Twist Pair 3	GRAY	5
8		PINK	8
7	Twist Pair 4	BLUE	7
10		RED	10
9	Twist Pair 5	ORANGE	9
2		LIGHT GREEN	2
11	Twist Pair 6	BLACK	11
12		VIOLET	12
SHELL		BRAID	SHELL

- Mueller's BU-1404940 is a shielded cable assembly that has a 12-position Male plug to 12-position female receptacle.
- Shell size for connector: M12 (A Coding)
- Cable Material: Polyurethane
 - Overall length = 16.4' (5m)
- Coupling Nut: Anodized Aluminum
- Rating:
 - Voltage: 30V AC/DC
 - Current: 1.5 Amps
 - Standard: IEC 61076-2-101
 - Waterproof: IP67/IP68
 - Temperature: -40°C to 105°C
- RoHS 3 Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-1404940](#)