

Han 3A-AK-Dichtung



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 20 003 5425 |
| Specification | Han 3A-AK-Dichtung |
| HARTING eCatalogue | https://b2b.harting.com/09200035425 |

Identification

| | |
|-----------------------------|-------------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A [®] |
| Type of hood/housing | Protection cover |
| Description of hood/housing | for bulkhead mounted housings |
| | for surface mounted housings |
| | Metal |
| | With fixing cord |
| | With seal |

Version

| | |
|----------------------|---|
| Locking type | Single locking lever |
| Size | 3 A |
| Field of application | Standard Hoods/housings for industrial applications |
| Details | for mounted female insert or for mounted Han-Brid [®] insert |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP44 |
| | IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E | 12 |

Material properties

| | |
|-----------------|-----------|
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |



Pushing Performance

Material properties

| | |
|-----------------------------|----|
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 23 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| eCl@ss | 27440208 Cap for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200035425](#)