

Parallel male thread coupler



Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 16 bar


Flow rate at 6 bar: 3686 l/min ($\Delta P = 0,6$ bar)

ID Passage: 11 mm

Temperature: -15°C to +70°C

Construction: Body : Stainless steel

Highlight: Anti-static, Excellent efficiency, Harsh conditions

	A	B	C	BSPP male thread	Parts Numbers
	(mm)	(mm)	(mm)		
	108,9	37	26	G 3/8	ISI 111152
	109,9	37	26	G 1/2	ISI 111153
	114,4	37	32	G 3/4	ISI 111154