

Parallel male thread coupler

Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 12 bar

Flow rate at 6 bar: 3686 l/min ($\Delta P = 0,6$ bar)


ID Passage: 11 mm

Temperature: -15°C to +70°C

Construction: Polyamide composite body

Highlight: Anti-static, Excellent efficiency, Non scratch



|  | BSP male thread | | Parts Numbers |
|--|-----------------|--|---------------|
| | G 3/8 | | ISI 111152EB |
| | G 1/2 | | ISI 111153EB |
| | G 3/4 | | ISI 111154EB |