

Hose tail coupler

Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 12 bar

Flow rate at 6 bar: 3686 l/min ($\Delta P = 0,6$ bar)


ID Passage: 11 mm

Temperature: -15°C to +70°C

Construction: Polyamide composite body

Highlight: Anti-static, Excellent efficiency, Non scratch



	For hose ID (mm)	Parts Numbers
	9	ISI 111809EB
	10	ISI 111810EB
	13	ISI 111813EB
	16	ISI 111816EB
	19	ISI 111819EB