

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 plug EM 24VAC/DC CL/GN/YE/RD



Part No.:	698.240.75
Series:	Kompakt 37



MECHANICAL DATA	
Height	209 mm
Diameter	38 mm
Materials	PC
Dome colour	Clear Green Red Yellow
Housing colour	Black
Protection category	IP65
Connection	M12 plug 8-pole
Cable entry	Membrane grommet
Cable entry minimum	d = 1 mm
Cable entry maximum	d = 9 mm
Tension relief	Pull-out protection
Type of fixing	Built-in mounting
Working temperature minimum	-20°C
Working temperature maximum	+50°C
UL Type Rating	Type 12 Type 4X
Weight with packaging	154 g
Product weight	100 g

ELECTRICAL DATA	
Operating voltage	24V
Operating voltage type	AC/DC
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	24 VDC
Rated operational current	135 mA
Rated inrush current	500 mA
Protection class	Protection class 2
Pollution degree	3 In the connection area: 2


OPTICAL DATA	
Light source	LED
Light colour	Green Red White Yellow

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 plug EM 24VAC/DC CL/GN/YE/RD

Optical signal image	Permanent
Service life optical	50,000 h maximum

DRAWING



698/699

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.