

Completely pre-assembled Signal Towers / KOMPAKT 37  
**K37 plug EM Pulse tone 24VAC/DC CL/GN/YE**



|           |            |
|-----------|------------|
| Part No.: | 699.240.75 |
| Series:   | Kompakt 37 |



| MECHANICAL DATA             |                                 |
|-----------------------------|---------------------------------|
| Height                      | 209 mm                          |
| Diameter                    | 38 mm                           |
| Materials                   | PC                              |
| Dome colour                 | Clear<br>Green<br>Red<br>Yellow |
| Housing colour              | Black                           |
| Protection category         | IP65                            |
| Connection                  | M12 plug 8-pole                 |
| Cable entry                 | Membrane grommet                |
| Cable entry minimum         | d = 1 mm                        |
| Cable entry maximum         | d = 9 mm                        |
| Tension relief              | Pull-out protection             |
| Type of fixing              | Built-in mounting               |
| Working temperature minimum | -20°C                           |
| Working temperature maximum | +50°C                           |
| UL Type Rating              | Type 12<br>Type 4X              |
| Weight with packaging       | 156 g                           |
| Product weight              | 102 g                           |

| ELECTRICAL DATA             |                                |
|-----------------------------|--------------------------------|
| Operating voltage           | 24V                            |
| Operating voltage type      | AC/DC                          |
| Operating voltage frequency | 50Hz                           |
| Operating voltage tolerance | +/- 10%                        |
| Rated operational voltage   | 24 VDC                         |
| Rated operational current   | 160 mA                         |
| Rated inrush current        | 500 mA                         |
| Protection class            | Protection class 2             |
| Pollution degree            | 3<br>In the connection area: 2 |

| OPTICAL DATA |                                 |
|--------------|---------------------------------|
| Light source | LED                             |
| Light colour | Green<br>Red<br>White<br>Yellow |


! For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.

Completely pre-assembled Signal Towers / KOMPAKT 37  
**K37 plug EM Pulse tone 24VAC/DC CL/GN/YE**

|                      |                  |
|----------------------|------------------|
| Optical signal image | Permanent        |
| Service life optical | 50,000 h maximum |

| ACUSTICAL DATA                |                 |
|-------------------------------|-----------------|
| Volume/dB(max) at 1m distance | 85,0 dB (A)     |
| Acoustic signal image         | Pulse tone      |
| Audio frequency               | 2900 Hz         |
| Acoustic service life         | 5,000 h minimum |

**DRAWING**



! For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.