

# Bocube

Enclosures, polycarbonate UL 94 V0, crystal-clear lid



B 261704 PC-V0-G 7035

Order no.: 96026345

\* = Available on request.

## Characteristics

Colour of enclosure group  
Light grey, similar to RAL 7035

Colour of enclosure group  
Light grey

Protection class  
IP 66, 68 - 1,2m (2 hours)

Enclosure Material

ABS or PC UL 94 V0 (material is suitable for outdoor use; f1-listing according to UL 746C)

PU seal, foamed; for details please see Technical Information

Scope of delivery

Lid and base, hinged quick-release catches

## Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

## Technical documentation / Downloads

### Technical drawings

3D product data in STEP format: 96026345 B-261704-PC-V0-G-7035.stp (8.1 MB)


Drawing for mechanical processing: 96026345 B-261704-PC-V0-G-7035-G.dxf (3.1 MB)

28.01.2021

## Dimensions

Dimensions  
271 x 170 x 40 mm

Product drawing



### Product information

Bocube GB.pdf (1.9 MB)

Highlights Bocube.pdf (3.8 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product drawing in PDF format: 96026345 B-261704-PC-V0-G-7035.pdf (231.9 KB)

Product drawing in DXF format: 96026345 B-261704-PC-V0-G-7035.dxf (3.8 MB)

## Works Test Certificates

688 WPZ-Bocube-PC-V0 DE.pdf (184.6 KB)

689 WPZ-Bocube-ABS DE.pdf (165.1 KB)

689 WPZ-Bocube-ABS EN.pdf (160.3 KB)

688 WPZ-Bocube-PC-V0 EN.pdf (179.1 KB)

## Matching accessories

---



### Hinged quick-release catches (Set), polycarbonate UL 94 V0 or ABS

96310300	B SC 17 PC-V0 3000	For B 2617..	Flame red
96310302	B SC 17 PC-V0 5002	For B 2617..	Ultramarine blue
96310309	B SC 17 PC-V0 6029	For B 2617..	Mint green
96310304	B SC 17 PC-V0 7024	For B 2617..	Graphite grey
96310305	B SC 17 PC-V0 7035	For B 2617..	Light grey
96310303	B SC 17 PC-V0 1023	For B 2617..	Traffic yellow



### Hand-operated hinged catch (set), polycarbonate UL 94 V0 or ABS

96910300	B SC HB 17 PC-V0 3000	For B 2617..	Flame red
96910302	B SC HB 17 PC-V0 5002	For B 2617..	Ultramarine blue
96910309	B SC HB 17 PC-V0 6029	For B 2617..	Mint green
96910304*	B SC HB 17 PC-V0 7024	For B 2617..	Graphite grey
*			
96910305*	B SC HB 17 PC-V0 7035	For B 2617..	Light grey
*			
96910303	B SC HB 17 PC-V0 1023	For B 2617..	Traffic yellow




### Wall brackets

96510004	B WL 7024	For B 08... - B 26...	Graphite grey
96510005	B WL 7035	For B 08... - B 26...	Light grey



### Mounting panels, laminated paper, 2 mm

96606300	B M 2617	For B 2617..
----------	----------	--------------



### Sets of screws

96300000	B SHR	D (for optional screwing of enclosures B 0808 - 2617)
96600010	B M-SHR	C (for fixing mounting panels B M 1008-2736)
96700000	B FP-SHR	A (for fixing front panels)



#### Distance bolts

96708000 DIBLZ AK 30x5/IM3/8 ND = 2,4 - 2,6, for B...04



#### Blanking plugs to determine the hinge side

96410000 B VS 3000 Flame red  
96410005 B VS 7035 Light grey  
96410004 B VS 7024 Graphite grey



#### DIN rail acc. to DIN EN 60715 TH 15

22152301 TS 15 For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)



#### DIN rail acc. to DIN EN 60715 G 32

22322301 TS 32 For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)



#### DIN rail acc. to DIN EN 60715 TH 35

22352301 TS 35 For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)



#### Pressure compensation membrane DAE

52011000 DAE-D11 Self-adhesive membrane ø 11 mm