

# Bocube

Enclosures, ABS, single-coloured



B 261704 ABS 7035

Order no.: 96036345

\* = Available on request.

## Characteristics

Colour of enclosure group

Light grey, similar to RAL 7035

Colour of enclosure group

Light grey

Protection class

IP 66, 68 - 1,2m (2 hours)

Enclosure Material

ABS or PC UL 94 V0 (material is suitable for outdoor use; f1-listing according to UL 746C)

PU seal, foamed; for details please see Technical Information

Scope of delivery

Lid and base, hinged quick-release catches

## Note

Material shrinkage may result in ABS enclosures being approx. 0.1 - 0.25 % larger.

## Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.


» Additional information

## Dimensions

Dimensions

271 x 170 x 40 mm

Product drawing



## Technical documentation / Downloads

---

### Technical drawings

3D product data in STEP format: 96036345 B-261704-ABS-7035.stp (8.1 MB)  
Drawing for mechanical processing: 96036345 B-261704-ABS-7035-G.dxf (3.1 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product drawing in PDF format: 96036345 B-261704-ABS-7035.pdf (231.9 KB)

Product drawing in DXF format: 96036345 B-261704-ABS-7035.dxf (3.8 MB)

### Product information

Bocube GB.pdf (1.9 MB)  
Highlights Bocube.pdf (3.8 MB)

### Works Test Certificates

688 WPZ-Bocube-PC-V0 DE.pdf (184.6 KB)

689 WPZ-Bocube-ABS DE.pdf (165.1 KB)

689 WPZ-Bocube-ABS EN.pdf (160.3 KB)

688 WPZ-Bocube-PC-V0 EN.pdf (179.1 KB)

## Matching accessories

---



### Hinged quick-release catches (Set), polycarbonate UL 94 V0 or ABS

96330300	B SC 17 ABS 3000	For B 2617..	Flame red
96330302	B SC 17 ABS 5002	For B 2617..	Ultramarine blue
96330309	B SC 17 ABS 6029	For B 2617..	Mint green
96330304	B SC 17 ABS 7024	For B 2617..	Graphite grey
96330305	B SC 17 ABS 7035	For B 2617..	Light grey
96330303	B SC 17 ABS 1023	For B 2617..	Traffic yellow



### Hand-operated hinged catch (set), polycarbonate UL 94 V0 or ABS

96930300	B SC HB 17 ABS 3000	For B 2617..	Flame red
96930302	B SC HB 17 ABS 5002	For B 2617..	Ultramarine blue
96930309	B SC HB 17 ABS 6029	For B 2617..	Mint green
96930304*	B SC HB 17 ABS 7024	For B 2617..	Graphite grey
*			
96930305*	B SC HB 17 ABS 7035	For B 2617..	Light grey
*			
96930303	B SC HB 17 ABS 1023	For B 2617..	Traffic yellow



### Wall brackets

96510004	B WL 7024	For B 08... - B 26...	Graphite grey
96510005	B WL 7035	For B 08... - B 26...	Light grey



### Mounting panels, laminated paper, 2 mm

96606300	B M 2617	For B 2617..	
----------	----------	--------------	--



#### Sets of screws

96300000	B SHR	D (for optional screwing of enclosures B 0808 - 2617)
96600010	B M-SHR	C (for fixing mounting panels B M 1008-2736)
96700000	B FP-SHR	A (for fixing front panels)



#### Distance bolts

96708000	DIBLZ AK 30x5/IM3/8	ND = 2,4 - 2,6, for B...04
----------	---------------------	----------------------------



#### Blanking plugs to determine the hinge side

96410000	B VS 3000	Flame red
96410005	B VS 7035	Light grey
96410004	B VS 7024	Graphite grey



#### DIN rail acc. to DIN EN 60715 TH 15

22152301	TS 15	For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)
----------	-------	---



#### DIN rail acc. to DIN EN 60715 G 32

22322301	TS 32	For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)
----------	-------	---



#### DIN rail acc. to DIN EN 60715 TH 35

22352301	TS 35	For EM/ET 224, EM/ET 233-236, EM/ET 239-242, B 2617.., B 2736.. (crosswise)
----------	-------	---



#### Pressure compensation membrane DAE

52011000	DAE-D11	Self-adhesive membrane ø 11 mm
----------	---------	--------------------------------