

Completely pre-assembled Signal Towers / KOMPAKT 37

K37cl sr plug EM 24VAC/DC BU/CL/GN/YE/RD



Part No.:	698.460.75
Series:	Kompakt 37



MECHANICAL DATA		
Height	243 mm	
Diameter	38 mm	
Materials	PC	
Dome colour	Clear	
Housing colour	Silver	
Protection category	IP65	
Connection	M12 plug 8-pole	
Cable entry	Membrane grommet	
Cable entry minimum	d = 1 mm	
Cable entry maximum	d = 9 mm	
Tension relief	Pull-out protection	
Type of fixing	Built-in mounting	
Working temperature minimum	-20°C	
Working temperature maximum	+50°C	
UL Type Rating	Type 12 Type 4X	
Weight with packaging	172 g	
Product weight	118 g	

ELECTRICAL DATA		
Operating voltage	24V	
Operating voltage type	AC/DC	
Operating voltage frequency	50Hz	
Operating voltage tolerance	+/- 10%	
Rated operational voltage	24 VDC	
Rated operational current	175 mA	
Rated inrush current	500 mA	
Protection class	Protection class 2	
Pollution degree	3 In the connection area: 2	


OPTICAL DATA		
Light source	LED	
Light colour	Blue Green Red White Yellow	
Optical signal image	Permanent	
Service life optical	50,000 h maximum	

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



Completely pre-assembled Signal Towers / KOMPAKT 37

K37cl sr plug EM 24VAC/DC BU/CL/GN/YE/RD



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.