


FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 0.5 m

Commercial data

Item number	2289065
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	C421
Product key	CK2131
Catalog page	Page 536 (C-5-2019)
GTIN	4017918057459
Weight per piece (including packing)	90.4 g
Weight per piece (excluding packing)	87 g
Customs tariff number	85444290
Country of origin	DE

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Supported controller SIEMENS S7-1500

Suitable I/O card	6ES7521-1BL00-0AB0
	6ES7521-1BL10-0AA0
	6ES7522-1BL00-0AB0
	6ES7522-1BL01-0AB0
	6ES7522-1BL10-0AA0
	6ES7523-1BL00-0AA0
	6ES7531-7KF00-0AB0
	6ES7531-7LH00-0AB0
	6ES7531-7MH00-0AB0
	6ES7531-7NF00-0AB0
	6ES7531-7NF10-0AB0
	6ES7531-7PF00-0AB0
	6ES7532-5HF00-0AB0

Supported controller SIEMENS S7-300 / ET 200 M

Suitable I/O card	CPU 313C
	CPU 313C-2DP
	CPU 313C-2PtP
	CPU 314C-2DP
	CPU 314C-2PtP
	6ES7321-1BL00-0AA0
	6ES7322-1BL00-0AA0

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

	6ES7322-8BH01-0AB0
	6ES7323-1BL00-0AA0
	6ES7331-1KF01-0AB0
	6ES7331-7NF00-0AB0
	6ES7331-7NF10-0AB0
	6ES7331-7PF01-0AB0
	6ES7331-7PF11-0AB0
	6ES7332-5HF00-0AB0
	6ES7350-2AH01-0AE0
	6ES7357-4AH01-0AE0

Supported controller SIEMENS S7-400

Suitable I/O card	6ES7421-1BL01-0AA0
	6ES7421-7BH01-0AB0
	6ES7421-7DH00-0AA0
	6ES7422-1BL00-0AA0
	6ES7422-7BL00-0AB0
	6ES7431-0HH0-0AB0
	6ES7431-1KF00-0AB0
	6ES7431-1KF10-0AB0
	6ES7431-1KF20-0AB0
	6ES7431-7KF00-0AB0
	6ES7431-7KF10-0AB0
	6ES7431-7QH00-0AB0
	6ES7432-1HF00-0AB0

Supported controller SCHNEIDER ELECTRIC Modicon TSX QUANTUM

Suitable I/O card	DDI 353
	DDI 841
	DDI 853
	DAI 340
	DAI 440
	DAI 453
	DDO 353
	DDM 390
	ACI 030
	ACI 040
	ATI 030
	ARI 030
	AVI 030
	ACO 020
	ACO 130
	AVO 020
	EHC 105
	EHC 202

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Supported controller ALLEN-BRADLEY ControlLogix

Suitable I/O card	1756-IA16I
	1756-IB16D
	1756-IB16I
	1756-IB32
	1756-IH16I
	1756-OB32
	1756-IF8
	1756-IF16
	1756-HSC
	1756-M02AE

Supported controller HONEYWELL Experion PKS C200

Suitable I/O card	TC-IDK 161
	TC-IDX 161
	TC-IDJ 161
	TC-IDD 321
	TC-ODD 321
	TC-IAH 161

Cable/line

Cable length	0.5 m
--------------	-------

50X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	50
Shielded	no
Cable type	50X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	50x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	10.30 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	86 mm
Smallest bending radius, movable installation	161 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no

IEC 60332-1-2 (raw cable)

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Flame resistance	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

color code

IDC/FLK50 (1)	IDC/FLK50 (1) = black
IDC/FLK50 (2)	IDC/FLK50 (2) = brown
IDC/FLK50 (3)	IDC/FLK50 (3) = red
IDC/FLK50 (4)	IDC/FLK50 (4) = orange
IDC/FLK50 (5)	IDC/FLK50 (5) = yellow
IDC/FLK50 (6)	IDC/FLK50 (6) = green
IDC/FLK50 (7)	IDC/FLK50 (7) = blue
IDC/FLK50 (8)	IDC/FLK50 (8) = violet
IDC/FLK50 (9)	IDC/FLK50 (9) = gray
IDC/FLK50 (10)	IDC/FLK50 (10) = white
IDC/FLK50 (11)	IDC/FLK50 (11) = white-black
IDC/FLK50 (12)	IDC/FLK50 (12) = white-brown
IDC/FLK50 (13)	IDC/FLK50 (13) = white-red
IDC/FLK50 (14)	IDC/FLK50 (14) = white-orange
IDC/FLK50 (15)	IDC/FLK50 (15) = white-yellow
IDC/FLK50 (16)	IDC/FLK50 (16) = white-green
IDC/FLK50 (17)	IDC/FLK50 (17) = white-blue
IDC/FLK50 (18)	IDC/FLK50 (18) = white-violet
IDC/FLK50 (19)	IDC/FLK50 (19) = white-gray
IDC/FLK50 (20)	IDC/FLK50 (20) = brown-black
IDC/FLK50 (21)	IDC/FLK50 (21) = brown-red
IDC/FLK50 (22)	IDC/FLK50 (22) = brown-orange
IDC/FLK50 (23)	IDC/FLK50 (23) = brown-yellow
IDC/FLK50 (24)	IDC/FLK50 (24) = brown-green
IDC/FLK50 (25)	IDC/FLK50 (25) = brown-blue
IDC/FLK50 (26)	IDC/FLK50 (26) = brown-violet
IDC/FLK50 (27)	IDC/FLK50 (27) = brown-gray
IDC/FLK50 (28)	IDC/FLK50 (28) = brown-white
IDC/FLK50 (29)	IDC/FLK50 (29) = green-black
IDC/FLK50 (30)	IDC/FLK50 (30) = green-brown
IDC/FLK50 (31)	IDC/FLK50 (31) = green-red
IDC/FLK50 (32)	IDC/FLK50 (32) = green-orange
IDC/FLK50 (33)	IDC/FLK50 (33) = green-blue
IDC/FLK50 (34)	IDC/FLK50 (34) = green-violet
IDC/FLK50 (35)	IDC/FLK50 (35) = green-gray
IDC/FLK50 (36)	IDC/FLK50 (36) = green-white
IDC/FLK50 (37)	IDC/FLK50 (37) = yellow-black

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

IDC/FLK50 (38)	IDC/FLK50 (38) = yellow-brown
IDC/FLK50 (39)	IDC/FLK50 (39) = yellow-red
IDC/FLK50 (40)	IDC/FLK50 (40) = yellow-orange
IDC/FLK50 (41)	IDC/FLK50 (41) = yellow-blue
IDC/FLK50 (42)	IDC/FLK50 (42) = yellow-violet
IDC/FLK50 (43)	IDC/FLK50 (43) = yellow-gray
IDC/FLK50 (44)	IDC/FLK50 (44) = yellow-white
IDC/FLK50 (45)	IDC/FLK50 (45) = gray-black
IDC/FLK50 (46)	IDC/FLK50 (46) = gray-brown
IDC/FLK50 (47)	IDC/FLK50 (47) = gray-red
IDC/FLK50 (48)	IDC/FLK50 (48) = gray-orange
IDC/FLK50 (49)	IDC/FLK50 (49) = gray-yellow
IDC/FLK50 (50)	IDC/FLK50 (50) = gray-green

Connection data

Connection 1

Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Notes


General	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
---------	--

2289065

<https://www.phoenixcontact.com/us/products/2289065>

Drawings

Diagram



Maximum permissible current per path in uncoiled state

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2289065>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: FILE E 238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-



cUL Listed

Approval ID: FILE E 238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

cULus Listed

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Classifications

ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FLK 50/EZ-DR/ 50/KONFEK - Cable



2289065

<https://www.phoenixcontact.com/us/products/2289065>

Accessories

KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 x 8 mm

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com