

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 6 m



Your advantages

- Unshielded

Commercial data

Item number	2299440
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK2131
Catalog page	Page 567 (C-5-2019)
GTIN	4017918886165
Weight per piece (including packing)	603.9 g
Weight per piece (excluding packing)	567.3 g
Customs tariff number	85444290
Country of origin	DE

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Cable/line

Cable length	6 m
--------------	-----

26X0.14 [PVC]

Number of positions	26
Shielded	no
Cable type	26X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	26x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	8.30 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	70 mm
Smallest bending radius, movable installation	131 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

color code

IDC/FLK26 (1)	IDC/FLK26 (1) = black
IDC/FLK26 (2)	IDC/FLK26 (2) = brown
IDC/FLK26 (3)	IDC/FLK26 (3) = red
IDC/FLK26 (4)	IDC/FLK26 (4) = orange
IDC/FLK26 (5)	IDC/FLK26 (5) = yellow
IDC/FLK26 (6)	IDC/FLK26 (6) = green
IDC/FLK26 (7)	IDC/FLK26 (7) = blue
IDC/FLK26 (8)	IDC/FLK26 (8) = violet
IDC/FLK26 (9)	IDC/FLK26 (9) = gray
IDC/FLK26 (10)	IDC/FLK26 (10) = white
IDC/FLK26 (11)	IDC/FLK26 (11) = white-black
IDC/FLK26 (12)	IDC/FLK26 (12) = white-brown
IDC/FLK26 (13)	IDC/FLK26 (13) = white-red
IDC/FLK26 (14)	IDC/FLK26 (14) = white-orange
IDC/FLK26 (15)	IDC/FLK26 (15) = white-yellow
IDC/FLK26 (16)	IDC/FLK26 (16) = white-green
IDC/FLK26 (17)	IDC/FLK26 (17) = white-blue
IDC/FLK26 (18)	IDC/FLK26 (18) = white-violet
IDC/FLK26 (19)	IDC/FLK26 (19) = white-gray
IDC/FLK26 (20)	IDC/FLK26 (20) = brown-black
IDC/FLK26 (21)	IDC/FLK26 (21) = brown-red
IDC/FLK26 (22)	IDC/FLK26 (22) = brown-orange
IDC/FLK26 (23)	IDC/FLK26 (23) = brown-yellow
IDC/FLK26 (24)	IDC/FLK26 (24) = brown-green
IDC/FLK26 (25)	IDC/FLK26 (25) = brown-blue
IDC/FLK26 (26)	IDC/FLK26 (26) = brown-violet

Connection data

Connection 1

Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Connection 2


Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Notes

General	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
---------	--

Drawings

Diagram



Maximum permissible current per path in uncoiled state

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2299440>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: FILE E 238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-



cUL Listed

Approval ID: FILE E 238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

cULus Listed

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Classifications

ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FLK 26/EZ-DR/ 600/KONFEK - Cable



2299440

<https://www.phoenixcontact.com/us/products/2299440>

Accessories

KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 x 8 mm

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com