



Cable Length*	Part Number							
	Plastic Version				Metallized Plastic Version		Die Cast Version	
L	Cat. 5e UTP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor UTP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable
0.5 m ± 0.02m	17-132424							
1 m ± 0.03m	17-130004	17-130014	17-130024	17-130034	17-130044	17-130054	17-130064	17-130074
1.2 m ± 0.03m	17-132504							
2 m ± 0.03m	17-10006	17-101234	17-103164	17-103204	17-10028	17-101264	17-100544	17-101294
3 m ± 0.03m	17-130084	17-130094	17-130104	17-130114	17-130124	17-130134	17-130144	17-130154
4 m ± 0.04m	17-10007	17-101244	17-103174	17-103214	17-10029	17-101274	17-100554	17-101304
5 m ± 0.05m	17-10008	17-101254	17-103184	17-103224	17-10030	17-101284	17-100564	17-101314
6 m ± 0.06m	17-160024	17-160034	17-160044	17-160054	17-160064	17-160074	17-160084	17-160094
7 m ± 0.07m	17-130994	17-131004	17-131014	17-131024	17-131034	17-131044	17-131054	17-131064
10 m ± 0.1m	17-103054	17-103064	17-103194	17-103234	17-103074	17-102254	17-103084	17-103094
12,5 m ± 0.15m	17-132824							
15 m ± 0.15m	17-130604	17-130614	17-130624	17-130634	17-130644	17-130654	17-130664	17-130674
18 m ± 0.18m				17-132084				
20 m ± 0.20m	17-132834					17-132124		
25 m ± 0.25m	17-132484							
30 m ± 0.30m		17-132134						17-132714
40 m ± 0.40m								17-132724
50 m ± 0.50m								17-132734

**Notes:**

- Electrical:
  - Meets EIA/TIA-568-C.2 Cat.5e Specification
  - Connector Operating Temperature: -40° C to +85° C
- Materials and Finish:
  - Coupling Ring: Polyester (Black), Metallized ABS or Die-cast (Nickel Plated); UL94 V-0
  - Plug Housing: Polyester (Black) or Metallized ABS (Nickel Plated); UL94 V-0
  - Interfacial Seal: Silicon, Color: White
  - Cable Gland: PA (Black) or Brass, Nickel Plated
  - Cable Gland Seal: NBR, Color: Black
  - Cable Gland Insert (Metal Version): Nylon, Color: White
  - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
  - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
  - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
  - RJ45 Modular Boot: PVC, Color: Black
  - Cable: See Part Number Table

\*Note: Special cable length up to 20m are available please contact factory, Cable length > 20m cannot guarantee to meet TIA/EIA-568-C.2 Cat. 5e Specification.

RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION  DOT NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified			Scale:	Dim. in
	Name	Title	Approval Date	Dimensional: Angles			Material: See Notes	
	r	1 x r	Feb/28/2016	Vincent Ke	2007	Date	Name	RJ45 Cat. 5e Ethernet Patch Cords Industrial to Standard
	q	1 x q	Mar/17/2017	Vincent ke	Draw.	Jul. 20	Vincent Ke	
	p	1 x p	Jan/17/2017	Vincent Ke	Appd.	Jul. 20	J. Chaudry	
	o	1 x o	Feb/18/2016	Vincent ke	Norm			
	n	1 x n	Nov/02/2015	Vincent Ke	D-old			
m	1 x m	Aug/13/2013	Vincent ke					
a	original							
Rev.	Changes	Date	Name			Drawing No.: 39K1A299	DIN A3 Sheet 1/1	
						Part No.: SEE P/N TABLE		