



(b) NOTES:

1. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY;  
PLATING: min. 30µm HARD GOLD over min. 50µm NICKEL  
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS: A1 - A4
5. CONNECTOR IS PART MARKED: 3009W4SCM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		scale:
				dim. in mm		2:1 (5:1)
				date	name	material:
				drawn 09.08.02	Parei	SEE NOTES
				appd. 09.08.02	Mickenbecker	title:
				norm		D-SUB COMBINATION FEMALE
				d-old		9W4S SOLDER CUP
4 x b	Ä5139	20.03.2014	K.H.			dwg no:
a	Original					13K1A673
rev.	description	date	name			DIN-A3
						sh: 1
						part no:
						3009W4SCM99A10X