





# SR/SRVO Snap Rivets



Mat'l: UL94 V2 Nylon 6, RMS-52		Mat'l: UL94 V0 Nylon 66/6, RMS-103	Standard Pack: 1,000 per bag								Fig. No.
Color: Black	Color: White	Color: Black	Hole Dia. "G"	Extraction Force lb.(kg) Typ.	Total Holding Thickness "F"	"A" Dia.	"B"	"C"	"D" Dia.	"E"	Fig. No.
SR-2024B	SR-2024W	SRVO-2024B	.083 - .087 (2.1 - 2.2)	6.6 (3)	.024 - .047 (0.6 - 1.2)	.165 (4.2)	.047 (1.2)	.09 (2.4)	.079 (2)	.11 (2.8)	1
SR-2032B	SR-2032W	SRVO-2032B			.051 - .079 (1.3 - 2)			.13 (3.2)		.15 (3.8)	
SR-2040B	SR-2040W	SRVO-2040B			.083 - .110 (2.1 - 2.8)			.16 (4)		.22 (5.5)	
SR-2048B	SR-2048W	SRVO-2048B			.114 - .142 (2.9 - 3.6)			.19 (4.8)		.22 (5.5)	
SR-2056B	SR-2056W	SRVO-2056B			.146 - .173 (3.7 - 4.4)			.22 (5.6)		.28 (7.2)	
SR-2064B	SR-2064W	SRVO-2064B	.173 - .197 (4.4 - 5)	.25 (6.4)	.28 (7.1)						
SR-2632B	SR-2632W	SRVO-2632B	.106 - .110 (2.7 - 2.8)	11.0 (5)	.039 - .079 (1 - 2)	.197 (5)	.13 (3.2)	.106 (2.6)	.18 (4.5)		
SR-2642B	SR-2642W	SRVO-2642B			.079 - .118 (2 - 3)		.17 (4.2)		.18 (4.5)		
SR-2648B	SR-2648W	SRVO-2648B			.106 - .142 (2.7 - 3.6)		.19 (4.8)		.24 (6.1)		
SR-2655B	SR-2655W	SRVO-2655B			.134 - .169 (3.4 - 4.3)		.22 (5.6)		.24 (6.1)		
SR-2664B	SR-2664W	SRVO-2664B			.169 - .205 (4.3 - 5.2)		.25 (6.4)		.31 (7.8)		
SR-2672B	SR-2672W	SRVO-2672B	.201 - .236 (5.1 - 6)	.28 (7.2)	.31 (7.8)						
SR-3035B	SR-3035W	SRVO-3035B	.122 - .126 (3.1 - 3.2)	17.6 (8)	.039 - .079 (1 - 2)	.252 (6.4)	.14 (3.5)	.118 (3)	.20 (5.1)		
SR-3045B	SR-3045W	SRVO-3045B			.079 - .118 (2 - 3)		.18 (4.5)		.24 (6.1)		
SR-3055B	SR-3055W	SRVO-3055B			.118 - .157 (3 - 4)		.22 (5.6)		.24 (6.1)		
SR-3065B	SR-3065W	SRVO-3065B			.157 - .194 (4 - 5)		.26 (6.5)		.28 (7.1)		
SR-3075B	SR-3075W	SRVO-3075B			.197 - .236 (5 - 6)		.30 (7.5)		.35 (9)		
SR-3080B	SR-3080W	SRVO-3080B	.217 - .256 (5.5 - 6.5)	.32 (8)	.35 (9)						
SR-3090B	SR-3090W	SRVO-3090B	.256 - .295 (6.5 - 7.5)	.35 (9)	.43 (11)						
SR-3100B	SR-3100W	SRVO-3100B	.295 - .335 (7.5 - 8.5)	.39 (10)	.43 (11)						
SR-3535B	SR-3535W	SRVO-3535B	.142 - .146 (3.6 - 3.7)	26.4 (12)	.047 - .083 (1.2 - 2.1)	.252 (6.4)	.14 (3.5)	.138 (3.5)	.20 (5.1)		
SR-3545B	SR-3545W	SRVO-3545B			.083 - .118 (2.1 - 3)		.18 (4.5)		.24 (6.1)		
SR-3550B	SR-3550W	SRVO-3550B			.106 - .142 (2.7 - 3.6)		.20 (5)		.24 (6.1)		
SR-3555B	SR-3555W	SRVO-3555B			.118 - .157 (3 - 4)		.22 (5.6)		.28 (7.1)		
SR-3560B	SR-3560W	SRVO-3560B			.146 - .181 (3.7 - 4.6)		.24 (6)		.28 (7.1)		
SR-3570B	SR-3570W	SRVO-3570B	.177 - .217 (4.5 - 5.5)	.28 (7.2)	.35 (9)						
SR-3580B	SR-3580W	SRVO-3580B	.217 - .256 (5.5 - 6.5)	.32 (8)	.36 (9.1)						
SR-4050B	SR-4050W	SRVO-4050B	.161 - .165 (4.1 - 4.2)	44.0 (20)	.098 - .138 (2.5 - 3.5)	.315 (8)	.20 (5)	.157 (4)	.28 (7.1)		
SR-4060B	SR-4060W	SRVO-4060B			.138 - .177 (3.5 - 4.5)		.24 (6)		.28 (7.1)		
SR-4070B	SR-4070W	SRVO-4070B			.177 - .217 (4.5 - 5.5)		.28 (7.2)		.35 (9)		
SR-4080B	SR-4080W	SRVO-4080B			.217 - .256 (5.5 - 6.5)		.32 (8)		.35 (9)		
SR-4090B	SR-4090W	SRVO-4090B			.256 - .295 (6.5 - 7.5)		.35 (9)		.43 (11)		
SR-4100B	SR-4100W	SRVO-4100B	.295 - .335 (7.5 - 8.5)	.39 (10)	.43 (11)						
SR-4120B	SR-4120W	SRVO-4120B	.354 - .413 (9 - 10.5)	.47 (12)	.55 (14)						
SR-5045B	SR-5045W	SRVO-5045B	.201 - .205 (5.1 - 5.2)	55.0 (25)	.059 - .098 (1.5 - 2.5)	.354 (9)	.18 (4.5)	.197 (5)	.26 (6.5)		
SR-5055B	SR-5055W	SRVO-5055B			.098 - .138 (2.5 - 3.5)		.22 (5.6)		.26 (6.5)		
SR-5065B	SR-5065W	SRVO-5065B			.138 - .177 (3.5 - 4.5)		.26 (6.5)		.34 (8.5)		
SR-5075B	SR-5075W	SRVO-5075B			.177 - .217 (4.5 - 5.5)		.30 (7.5)		.34 (8.5)		
SR-5085B	SR-5085W	SRVO-5085B			.217 - .256 (5.5 - 6.5)		.34 (8.5)		.41 (10.5)		
SR-5095B	SR-5095W	SRVO-5095B	.256 - .295 (6.5 - 7.5)	.37 (9.5)	.41 (10.5)						
SR-5105B	SR-5105W	SRVO-5105B	.295 - .335 (7.5 - 8.5)	.41 (10.5)	.47 (12)						
SR-6060B	SR-6060W	SRVO-6060B	.240 - .244 (6.1 - 6.2)	66.0 (30)	.098 - .157 (2.5 - 4)	.472 (12)	.098 (2.5)	.236 (6)	.35 (9)		
SR-6080B	SR-6080W	SRVO-6080B			.138 - .217 (3.5 - 5.5)		.118 (3)		.39 (10)		