

Material number	0 601 063 S00
EAN	3165140888356
Retail price	312.33 GBP
Discount Group	GDM
4 x 1.5 V AA	✓
Carrying case	✓
Laser target plate	✓
Pouch	✓



Technical data

Description

Outdoor applications	Alignment Pulse mode
Indoor applications	Drywall installation Suspended ceiling installation Interior fitting work Levelling work Floor and wall tiles Fitting cabinets and shelves



Technical data

Laser diode	Line: 630 - 650 nm, < 10mW
Operating temperature	-10 – 40 °C
Storage temperature	-20 – 70 °C
Laser class	2
Working range	30 m
Working range with receiver	120 m
Working range without receiver	30 m
Accuracy	± 0.2 mm/m
Self-levelling range	± 4°
Levelling time	4 s
Dust and splash protection	IP 54
Power supply	4 x 1.5 V LR6 (AA)
Operating time (max.)	4 h in 3-line mode
Tripod thread	1/4", 5/8"
Weight, approx.	0.82 kg
Colour of laser line	red
Projection	3 x 360° line

Sales information

Positioning

- Visibility on a new level in 3 x 360°

User benefit

- High visibility due to high power diodes
- High work efficiency due to 3 x 360° lines: Simultaneous performance of horizontal and vertical levelling applications in the entire room with only one tool
- Easy to operate using intuitive user interface

Other features

- Self-levelling (4° in 4 sec) and very precise (± 0.2 mm/m)
- Working range of 80 m with the LR 6 or LR 7 Professional receiver (optional)
- Compact, easy to handle and extremely robust (IP54)
- Pendulum lock ensures safe transport