

FEATURES

- Filter / regulator
- Manual drain
- With metal bowl guard

RS PRO

Filter / Regulator With metal bowl guard

RS Stock No.: 2351145



Metal drain

Product Description

Part No.	Body Size	Port Size	Flow Rate (l/min)
2351145	4000	1/2"	5211

Features

- Filter / regulator
- Manual drain
- With metal bowl guard

General Specifications

Max. working pressure	10 bar
Temperature range	+5°C to +60°C
Filter precision	25 micron
Max. inlet pressure	15 bar
Adjustable pressure range	0.5 to 8.5 bar

Materials

Bowl	Polycarbonate with metal bowl guard
-------------	-------------------------------------