



Basic features

Approval/Conformity	cURus EAC WEEE
---------------------	----------------------

Electrical connection

Cable diameter D	2.9...5.1 mm
Connection	M12x1-Female, Straight, 5-pin, A-coded
Number of connectable contacts	4
System	Can be fabricated

Electrical data

Operating voltage U_b	32 VDC / 32 VAC
Rated current (40 °C)	4.0 A

Environmental conditions

Ambient temperature	-40...85 °C
IP rating	IP67

Remarks

max. connection frequency with same cable cross-section 10
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Material

Conductor insulation material	PVC PP TPE
Housing material	PA
Material contact carrier	PA
Material contacts	Brass
Material cover nut	Brass nickel-plated
Material grip	Plastic

Mechanical data

Conductor diameter min.	1 mm
Connection cross-section	0.14...0.34 mm ²
Connection cycles min.	100
Core diameter max.	1.60 mm
Tightening torque pigtail	0.6 Nm
Type of wire mounting	IDC

Connector Drawings

