



РАЗЪЕМЫ СЕРИИ IDC



РАЗЪЕМЫ IDC, ШАГ 2.54 ММ

Розетка для наковки на плоский кабель с шагом 1.27 мм





Наименование	Размеры, мм	
	A	B
IDC-10F	17.27	10.16
IDC-14F	22.35	15.24
IDC-16F	24.89	17.78
IDC-20F	29.96	22.86
IDC-24F	35.05	27.97
IDC-26F	37.59	30.48
IDC-30F	42.67	35.56
IDC-34F	47.75	40.64
IDC-40F	55.37	48.26
IDC-50F	68.07	60.69
IDC-60F	80.77	73.66
IDC-64F	85.85	78.74

Вилка для пайки на плату





Наименование	Размеры, мм		
	A	B	C
IDC-10MS(MR)	20.34	18.10	10.16
IDC-14 MS(MR)	25.48	23.18	15.24
IDC-16 MS(MR)	27.90	25.72	17.78
IDC-20 MS(MR)	33.05	30.80	22.86
IDC-24 MS(MR)	38.08	35.88	27.94
IDC-26 MS(MR)	40.68	38.42	30.48
IDC-30 MS(MR)	45.70	43.50	35.56
IDC-34 MS(MR)	50.80	48.58	40.64
IDC-40 MS(MR)	58.46	56.20	48.26
IDC-50 MS(MR)	71.10	68.90	60.69
IDC-60 MS(MR)	83.80	81.60	73.66
IDC-64 MS(MR)	89.10	86.68	78.74

Вилка для наковки на плоский кабель с шагом 1.27 мм, открытая





Наименование	Размеры, мм	
	A	B
FDC-10	17.27	10.16
FDC-14	22.35	15.24
FDC-16	24.89	17.78
FDC-20	29.96	22.86
FDC-24	35.05	27.97
FDC-26	37.59	30.48
FDC-30	42.67	35.56
FDC-34	47.75	40.64
FDC-40	55.37	48.26
FDC-50	68.07	60.69
FDC-60	80.77	73.66
FDC-64	85.85	78.74

Вилка с фиксатором для наковки на плоский кабель с шагом 1.27 мм





Наим-е	Размеры, мм					
	A	B	C	D	E	F
IDCC-10	31.96	25.40	10.16	21.84	17.96	47.08
IDCC-14	37.10	30.48	15.24	26.92	23.04	52.18
IDCC-16	39.62	33.02	17.78	29.46	25.58	54.84
IDCC-20	44.74	38.10	22.86	34.54	30.66	59.90
IDCC-24	49.82	43.18	27.94	39.62	35.74	64.98
IDCC-26	52.22	48.26	30.48	42.16	38.28	67.24
IDCC-30	57.46	53.26	35.56	46.74	43.58	72.64
IDCC-34	62.52	58.42	40.64	52.32	48.44	77.48
IDCC-40	70.18	66.04	48.26	59.94	56.60	85.36
IDCC-50	82.74	78.74	60.96	72.64	68.76	97.90
IDCC-60	95.68	91.44	73.66	85.34	81.45	110.66
IDCC-64	100.70	96.52	78.74	90.42	86.54	115.62

Вилка с фиксатором для пайки на плату



Наименование	Размеры, мм			
	A	B	C	D
IDCC-10MS(MR)	31.88	10.16	21.84	17.96
IDCC-14 MS(MR)	37.02	15.24	26.92	23.04
IDCC-16 MS(MR)	39.52	17.78	29.46	25.58
IDCC-20 MS(MR)	44.74	22.86	34.54	30.66
IDCC-24 MS(MR)	50.08	27.94	39.48	36.03
IDCC-26 MS(MR)	52.20	30.48	42.16	38.28
IDCC-30 MS(MR)	57.40	35.56	47.24	43.36
IDCC-34 MS(MR)	62.40	40.64	52.32	48.44
IDCC-40 MS(MR)	70.04	48.26	59.94	56.60
IDCC-50 MS(MR)	82.72	60.96	72.64	68.76
IDCC-60 MS(MR)	95.40	73.66	85.34	81.46
IDCC-64 MS(MR)	100.50	78.74	90.42	86.54

Вилка для наковки на плоский кабель с шагом 1.27 мм, закрытая



Наименование	Размеры, мм				
	A	B	C	D	E
IDM-10(A)	36.84	25.52	21.24	18.10	10.16
IDM-14 (A)	41.90	30.58	26.30	23.24	15.24
IDM-16 (A)	44.40	33.20	29.86	25.78	17.78
IDM-20 (A)	49.30	38.04	33.82	30.86	22.86
IDM-24 (A)	54.64	43.34	39.12	35.94	27.94
IDM-26 (A)	57.24	45.92	41.60	38.50	30.48
IDM-30 (A)	62.32	51.04	46.70	43.62	35.56
IDM-34 (A)	66.98	55.70	51.58	48.60	40.64
IDM-40 (A)	75.02	63.70	59.50	56.36	48.26
IDM-50 (A)	87.38	76.10	71.94	69.90	60.96
IDM-60 (A)	100.52	89.24	84.94	81.88	73.66
IDM-64 (A)	105.64	94.32	90.00	86.90	78.74