




Metal Fan Guard




MODEL	A	B	C	D
K-G02C02-2PAU	28.2	3.2	24.0	2.5




MODEL	A	B	C	D
K-G03C02-4HA	24	3.2	21.8	4.8




MODEL	A	B	C	D
K-G0BD02-4HA	29	4.0	27	4.0



MODEL	A	B	C	D
K-G04D02-4HA	32	4.0	29.1	4.8




MODEL	A	B	C	D
K-G04B02-4HB	32	4.6	31.5	4.0




MODEL	A	B	C	D
K-G05B03-4HB	40	4.6	41.1	4.8


Metal Fan Guard




MODEL	A	B	C	D
K-G06B04-4HA	50	4.6	53	4.4




MODEL	A	B	C	D
K-G06B04-4HB	50	4.6	53	5.2




MODEL	A	B	C	D
K-G07F04-4HA	61.5	4.5	64.2	4.0



MODEL	A	B	C	D
K-G08A05-4HA	71.5	4.9	76	5.5




MODEL	A	B	C	D
K-G08B05-4HA	71.5	4.6	76	5.5




MODEL	A	B	C	D
K-G09A06-4HA	82.5	4.9	90	5.5


Metal Fan Guard




MODEL	A	B	C	D
K-G09B06-4HB	82.4	4.6	89.8	5.0




MODEL	A	B	C	D
K-G12B07-4HA	105	4.6	115.6	5.5




MODEL	A	B	C	D
K-G12B08-4HA	105	4.6	115.6	5.5



MODEL	A	B	C	D
K-G12A08-4HA	105	4.9	115.6	5.5




MODEL	A	B	C	D
K-G17H10-2HA	162	5.0	154.4	6.45




MODEL	A	B	C	D
K-G17H10-2HB	162	5.0	154.4	6.45

Plastic Fan Guard




Material:ABS

MODEL	A	B	C	D
K-PG06J-4PA	50	4.5	60	6.7




Material:ABS

MODEL	A	B	C	D
K-PG08J-4PA	71.5	5.0	81	50



Material:ABS


MODEL	A	B	C	D
K-PG09J-4PA	82.5	4.9	92	6.4




Material:ABS

MODEL	A	B	C	D
K-PG12J-4PA	104.5	5.0	119.5	6.4


Metal Fan Filter




MODEL	A	B	C	D
K-MF06E-4HA	50	4.32	60	4.0




MODEL	A	B	C	D
K-MF08E-4HA	71.4	4.32	83.8	3.5



MODEL	A	B	C	D
K-MF16E-2HA	162	4.3	182	4.15





MODEL	A	B	C	D
K-MF09E-4HA	82.5	4.32	92	4.0





MODEL	A	B	C	D
K-MF12E-4HA	104.8	4.32	118.9	3.5

Plastic Fan Filter

K-PF06J-4PA






K-PF08J-4PA






Plastic Fan Filter

K-PF09J-4PA




K-PF12J-4PA





Power Cord


19-1180 (TYPE STRAIGHT 180°)



19-1090 (TYPE 90°)



19-1045 (TYPE 45°)



STANDARD DIMENSIONS (mm)

Model	19-1180	19-1090	19-1045
Wire Length	900mm	900mm	900mm

*Wire length is adjustable by request.