


plug socket with cable KMEB-3-24-2,5-LED

Part number: 547268

FESTO

For VUVB solenoid valves with 24 V coils.



Data sheet

Feature	Value
Operating status display	Yellow LED
Mounting type	On solenoid valve with M2.5 central screw
Assembly position	Any
Product weight	120 g
Electrical connection	Plug socket angled Per DIN EN 175301-803 Plug pattern type C to EN 175301-803 2-pin
Nominal operating voltage DC	24 V
Polarity protected	for all electrical connections
Protective earth connection	Not available
Cable length	2.5 m
Cable attribute	Standard
Cable diameter	5.2 mm
Cable structure	2x0,75
Protection class	IP65 to IEC 60529
Ambient temperature	-20 ... 80 °C
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Corrosion resistance classification CRC	1 - Low corrosion stress
Material cable sheath	PVC
Material housing	PC
Material electrical contact	Bronze Silver plated