



Plastic:PC ,Core : PA66;

Copper: phosphor copper 0.8mm plated with tin;

Spring:Stainless Steel 0.4mm;

Rated voltage/current: 250V/32A;

Working temperature:-40°C - +105°C ;

Withstand Voltage:AC2000V/DC500V;

Insulation Resistance:500MΩ/DC500V;

Suitable cable cross sections:1mm²-6mm²;

Max.Drawing pressure:8Kg-10Kg;