

Plastic: Translucent PP,Core: PA66;

Copper: phosphor copper 0.8mm plated with tin;

Spring:Stainless Steel 0.4mm;

Rated voltage/current: 250V/24A;

Working temperature: $-40^{\circ}\text{C} - +105^{\circ}\text{C}$;

Withstand Voltage: AC2000V/DC500V;

Insulation Resistance: $500M\Omega/DC500V$;

Suitable cable cross sections:0.75mm²-2.5mm²;

Max.Drawing pressure:8Kg-10Kg;