



STYLE	UL2725 28#/1P+28#/2C+AEB		DOCUMENT NO.	VG/TSY-094-XXX
CONSTRUCTION ITEM		1P		2C
CONDUCTOR	SIZE	28AWG		28AWG
	MATERIAL	TC		TC
	CONSTRUCTION	7/0.12±0.008mm		7/0.12±0.008mm
INSULATION	AVG. THICK	0.24mm		0.24mm
	MIN. THICK	0.16mm		0.16mm
	MATERIAL	HDPE		SR-PVC
	DIAMETER	0.85±0.05mm		0.85±0.05mm
SHIELDED	FILLET SHIELD	-----		
	AL/MYLAR MATERIAL	AL/MYLAR		
	AL/MYLAR CONSTRUCTION	10/0.02mm		
	MYLAR MATERIAL	-----		
	MYLAR CONSTRUCTION	-----		
	DRAIN MATERIAL	TC		
	DRAIN CONSTRUCTION	7/0.12±0.008mm		
	BRAID MATERIAL	TC		
BRAID CONSTRUCTION	16/4/0.10±0.008mm			
COVERED	AVG. THICK	-----		
	MIN. THICK	-----		
	MATERIAL	-----		
	DIAMETER	-----		
	COLOR	-----		
JACKET	AVG. THICK	0.68mm		
	MIN. THICK	0.56mm		
	MATERIAL	65Pa 80°C UL-PVC ALL raw materials meet rohs standards		
	DIAMETER	3.80±0.15mm		
	COLOR	IV-29#(HALF ATOMIZER)		
MARKING	MARKING NO. 内容(287#)	HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C E189529  AWM STYLE 2725 80°C 30V VW-1 VEGA TECH		
	COLOR	BLACK		
CONSTRUCTION DRAWING & COLOR				
			芯线颜色: 1P: WHITE, GREEN 2C: REN (RD-01#), BLACK	
ELECTRICAL CHARACTERISTICS 电气特性				
1. Conductor Resistance: AT 20°C Max: 28AWG 237.25 Ω/KM 2. Insulation Resistance: AT 20°C Min: 10M Ω/KM 3. Dielectric Strength: AC500V 60HZ/分钟				