



Fuse-link, low voltage, 11 A, AC 1000 V, DC 1000 V, 10 x 38 mm, UL, fast-acting



Part no. **DMM FUSE - BUSSMANN**
 Catalog No. **DMM-B-11A**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	11
Rated voltage			AC 1000 V DC 1000 V
Size			10 x 38 mm
usable for size/applications			Multimeters only
Release characteristic	class		fast-acting
Standard/Approval			UL
Shape			cylindrical
Standards/Regulations			UL 248-14

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			10x38 mm
Rated voltage		V	1000 - 1000
Rated voltage			Other
Voltage type			AC/DC
Utilization category			Other
Rated operating frequency		Hz	45 - 62
Nominal current		A	11
With striker			No
Release characteristic			Other
Breaking capacity		kA	20

Additional product information (links)

Product datasheet (pdf)	http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-a/Bus_Ele_DS_1047_DMM-B.pdf
-------------------------	---