

74A - Forged socket wrenches with metric screwdriver handle





Standards:

NF ISO 2236, NF ISO 691, ISO 2236, ISO 691, DIN 3125, DIN ISO 691

Description:

- Socket wrenches with screwdriver handle ideal for screws with limited access in height or precision mechanics.
- Protwist screwdriver handle for optimum comfort even for powerful unlocking.
- 6-point socket with deep opening for long threads.
- Forged body for maximum strength.
- Metric sizes: 3.2 to 14 mm.
- Presentation: satin chrome finish.



	A [mm]	Diameter [mm]	Length L [mm]	Length L1 [mm]	Weight [Kg]
74AT.10	10.0	14.5	250.0	125.0	0.2
74AT.11	11.0	16.0	250.0	125.0	0.21
74AT.12	12.0	17.0	250.0	125.0	0.21
74AT.13	13.0	18.5	250.0	125.0	0.25
74AT.14	14.0	20.0	250.0	125.0	0.255
74AT.3.2	3.2				0.11
74AT.4	4.0	7.0	245.0	125.0	0.115
74AT.4.5	3.2				0.12
74AT.5	5.0	8.0	245.0	125.0	0.12
74AT.5.5	3.2				0.21
74AT.6	6.0	9.5	245.0	125.0	0.125
74AT.7	7.0	9.5	245.0	125.0	0.13
74AT.8	8.0	12.0	245.0	125.0	0.155
74AT.9	9.0	12.0	245.0	125.0	0.16