

通用继电器	HJQ-13F-2C
-------	------------

- 10A transfer contacts
- Different dust-proof cover,different layout
- Conform to RoHS,ELV directive

28×21.5×35



03001006458

us E173485

R50031316

ORDERING CODE 订购代码

HJQ-13F — 2Z — F (P) / 12VDC				
1	2	3	4	5
1. Relay Model 继电器型号				5. Coil Nominal Voltage 线圈额定电压
2. 触点转换形式				5,6,12,24,48,110,120VDC
2Z: Form 2C				6,12,24,48,110,220/240VAC
3. With Flange for 38mm pitch hole				
4. P: PCB Type				
Nil: B Type				

COIL DATA 线圈参数 (at 20°C)

Nominal Voltage额定电压(VDC)	5	6	12	24	48	110/120	220/240	0.9W
Coil Resistance线圈阻值(Ω)	28	40	160	640	2560	11000	/	
Rated Current额定电流(mA)	178.5	150	75	37.5	18.75	10	/	
Max Operate Voltage 最大吸合电压(VDC)	3.75	4.5	9	18	36	82.5	/	
Min Release Voltage最小释放电压(VDC)	0.5	0.6	1.2	2.4	4.8	11	/	
Nominal Voltage额定电压(VAC)		6	12	24	48	110/120	220/240	1.2VA
Coil Resistance线圈阻值(Ω)	/	11.5	46	180	735	4550	14400	
Max Operate Voltage 最大吸合电压(VAC)	/	4.8	9.6	19.2	38.4	96	176	
Min Release Voltage最小释放电压(VAC)	/	1.2	2.4	4.8	9.6	22	44	
Max Applicable Voltage 最大过载电压	70°C时额定电压的130%，23°C时额定电压的170%							

注：5-24VDC/6-48VAC 线圈阻值公差为±10%，48-110VDC/110-240VAC 线圈阻值公差为±15%。

CONTACT DATA 触点参数

Contact Form触点形式	2Z
Contact Material触点材料	Silver Alloy
Load负载	Resistive load(COS Φ=1)
Contact Ratings触点负载	10A 250VAC/30VDC
Minimum load 最小负载	100mA 5VDC
Max Switching Voltage最大转换电压	250VAC/30VDC
Max Switching Current最大转换电流	15A
Max Switching Power 最大转换功率	2500VA/300W
Contact Resistance接触电阻	100m Ω Max at 6VDC 1A
Life Expectancy寿命	Electrical 电气寿命: 100,000 Operations(at30Operations/minute)
	Mechanical机械寿命: 10,000,000 Operations(at300Operations/minute)


■ CHARACTERISTICS DATA 性能参数

Insulation Resistance绝缘阻值	100MΩ Min at 500VDC
Dielectric Strength Between Open Contacts触点间耐压	1000VAC(for one minute)
Between Contacts and coil触点与线圈间耐压	1500VAC(for one minute)
Operate Time吸合时间	25ms
Release Time释放时间	25ms
Temperature Range环境温度	-40°C to +70°C
Shock Resistance冲击	Operating Extremes动作极限: 20G
	Damage Limits破坏极限: 100G
Vibration Resistance振动	10-55Hz, 1.5mm
Max. switching frequency最大转换频率	Mechanical: 18,000operations/hr
	Electrical: 1,800operations/hr
Humidity湿度	40-85%
Weight重量	Approx 35g
Safety Standard安全标准	UL cUL TÜV CQC





■ APPROVED STANDARDS 安全标准

Model(型号)	Coiling rating (线圈电压)	Safety Standard (安全标准)	Contact rating (触点负载)
HJQ-13F-2C	5 to 110VDC	TÜV	10A 240VAC
	6 to 240VAC		10A 30VDC
	5 to 110VDC	UL/cUL	10A 250VAC
	6 to 240VAC		10A 30VDC 15A 125VAC
	5 to 110VDC	CQC	10A 240VAC
	6 to 240VAC		



■ ENGINEERING DATA 设计参数





OVERALL AND MOUNTING DIMENSIONS 安装图





B 型





P 型



B 型 (耳朵)



P 型 (耳朵)



接线图

声明:

本产品规格书仅供客户使用时参考，如有更改，恕不另行通知。