

SPECIFICATIONS:

MATERIALS:

HOUSING: TPU, BLACK

CONTACTS: **GOLD PLATED BRASS**

NUT: NICKEL PLATED BRASS SHELL: **NICKEL PLATED BRASS**

ORING: **EPDM**

ELECTRICAL:

RATED CURRENT: 2A RATED VOLTAGE: 30V

INSULATION RESISTANCE: 100 MOhms MIN. CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C

WATER PROOF:

IP67

0.532 [13.51] [10.01] 0.571 [14.51] M12×1.0 .394 0.024 [0.60] 0.418 [10.61] NUT

PIN 3

858-D04-203RSSY 3 = BRASS/NICKEL (B/N) SHELL & NUT -S = STAINLESS STEEL (SS) SHELL & NUT

T = B/N SHELL / SS NUT

1 = GOLD FLASH -

4 = 10u'' GDLD

ROHS COMPLIANT

PIN 4



THE PROPERTY OF NorComp AND SHALL NOT APPARATUS WITHOUT WRITTEN PERMISSION.

DESCRIPTION: M12 FEMALE - CABLE MOUNT - SOLDER CUP - 4 POS. - D CODE

DRAWN: M. SIGMON

DATE: 05/13/2016 UNITS = inch [mm]

DO NOT SCALE FROM DRAWING REV

NorComp

SCALE: SHEET OF NTS 1 DWG NO.

858-D04-203RSSY